


HM-4B schematic - lamps are 24 VDC 40 mA. - #85 switch is momentary operation. Use pre-wire connector HM-10P.

2-gang mounting rotate 90 degrees for proper orientation



HM-4B/K2 schematic - one of 4 identical circuits - lamps are 24 VDC 40 mA. - #85 switches are latching (push-on / push-off). Use pre-wire connectors HM-4P, 4 each

Heritage MedCall, Inc.  
 202 East Virginia Avenue  
 Tampa, FL 33603  
 813-221-1000 (voice)  
 813-223-1405 (fax)  
 www.heritagemedcall.com

Title HM-4B / HM-4B/K2 Pushbutton Panel		
Size A	Number	Rev
Date January 2003	Drawn by	
Filename 4B-4BK2.sch	Sheet of	