

TECHNICAL SPECIFICATIONS


TWENTY LAMP ANNUNCIATOR PANEL

HM-A20

*Displays System Status
Low-Power High-Visibility Lamps
Variety of Lens Colors Available
Connections via Prewired Connectors*



Front



Rear

DESCRIPTION

Wall recessed or surface mounted twenty lamp call annunciator panel providing visual system status indication via twenty lamp positions.

INDICATORS

Twenty low-power high visibility lamps. Standard lens color is white, others available separately include: red, amber, green, blue, yellow and clear.

Custom laminated labels are available for lenses.

Lamps are rated 24 VDC at 40 mA.

Lamps are front replaceable with rated average life of 6000 hours.

LISTINGS

The HM-A20 is UL and CUL listed Hospital Signaling Equipment / Nurse Call Equipment under File E157381.

INSTALLATION

Plugs into prewired connectors.

HM-A20 requires two HM-11P

Mounts onto backbox with four 6-32 x 1" nylon screws provided.

HOUSING AND FINISH

Faceplate: Punched aluminum faceplate with baked epoxy finish, finished in off-white.

DIMENSIONS

Faceplate: 8-1/2" (21.59cm) wide x 11" (27.94cm) high.

W2 Backbox: 7-1/2" (19.05cm) wide x 10" (25.4cm) high x 3 1/2" (8.89 cm) deep, available separately from Heritage.

Heritage Medcall, Inc.

202 East Virginia Avenue, Tampa, FL 33603
813-221-1000 (voice), 813-223-1405 (fax)
www.heritagemedcall.com

01/04 HM-A20 Issue C
Printed in U.S.A.

ARCHITECTS' AND ENGINEERS' SPECIFICATIONS

MODEL HM-A20 TWENTY POSITION ANNUNCIATOR PANEL

The wall recessed or surface mounted HM-A20 Twenty Position Annunciator Panel shall provide visual status indication via 20 lamp positions.

The panel shall provide twenty low-power high-visibility indicator lamps. Lamps shall be front panel replaceable with an average rated life of 6000 hours. Standard lens color shall be white. Others lens colors available separately shall be red, amber, green, blue, yellow, and clear.

The HM-A20 is UL and CUL listed Hospital Signaling Equipment / Nurse Call Equipment under File E157381.

The faceplate shall be metal, finished in off-white and flame retardant. For ease of installation, the annunciator panel shall plug into pre-wired connectors.

Faceplate shall mount to backbox with four 6-32 x 1" nylon screws provided.

Annunciator panel shall install into a W2 steel electrical backbox for wall flush mounting.

The dimensions shall be: **Faceplate** - 8-1/2" (21.59cm) wide x 11" (27.94cm) high; **W2 backbox** - 7-1/2" (19.05cm) wide x 10" (25.40cm) high x 3 1/2" (8.89cm) deep, for total depth of 3-3/4" (9.53cm), available from Heritage.