

# TECHNICAL SPECIFICATIONS

## LAMP AND TONE CONTROL UNIT

HM-T1

*Single Level Call*  
*Terminal Block for Connections*  
*Removable Protective Cover*  
*Metal Base for Easy Wall Mounting*  
*Rugged Metal Housing*



### DESCRIPTION

Single level lamp and tone control unit for multiple call locations to provide call event activation or de-activation from any call location.

### CIRCUITRY

Solid state for maximum reliability.

### OPERATING VOLTAGE

24 volts DC. No AC outlet required.

### OUTPUT RATING

Circuit draw 20 ma.  
Maximum draw 2 amps.

### INDICATORS

Power Indication  
Lamp Active  
Tone Active

### TONE RATES

Length: 0 - 1 seconds  
Rate: 1- 60 seconds

### INSTALLATION

Terminal block for wire connections with holes in base for wall mounting.

### HOUSING

Natural aluminum finished box 0.040 thickness.

### DIMENSIONS

5.25" L X 3.0" W X 2.12" H

### Heritage Medcall, Inc.

202 East Virginia Avenue, Tampa, FL 33603  
813-221-1000 (voice), 813-223-1405 (fax)  
www.heritagemedcall.com

07/04 HM-T1  
Printed in U.S.A.

---

## **MODEL HM-T1 LAMP AND TONE CONTROL UNIT**

The lamp and tone control unit shall consist of solid state circuitry in a surface mounted housing.

The lamp and tone control unit shall operate on 24-28 volts DC and shall not require an AC outlet. The output rating shall be maximum 2 amps at 24-28 volts DC.

The lamp and tone control unit shall have an adjustable tone duration from zero to one second.

The lamp and tone control unit shall have an adjustable tone rate from one to sixty seconds.

Installation shall consist of six position terminal block for wire connections and housed in a natural aluminum finished box 0.040" thickness.

Dimensions of housing shall be 5.25" L X 3.0" W X 2.12" H.