


TECHNICAL SPECIFICATIONS

CODE BLUE CALL SWITCH

HM-1B/K2 (Code Blue)

*Illuminated Pushbutton
Silk-Screened Labeled Code Blue
Connections via Prewired Connector*



DESCRIPTION

Wall recessed or surface mounted one button switch panel with silk-screened Code Blue Label. Latching switch.

CONTROLS AND INDICATORS

One combination pushbutton and lamp indicator. Standard lens color is blue others available separately include white, amber, green, red, yellow, clear, and black. Custom laminated labels are available for lenses. Lamps are front replaceable with rated average life of 6000 hours.

SWITCH

Switch is normally-open, single-pole / single throw. HM-1B/K2 (CODE BLUE) is latching (push-on / push-off). All switches are rated 1A / 125 VAC.

INSTALLATION

Plugs into prewired connectors. HM-1B/K2 (CODE BLUE) requires one HM-4P Mount using only the two 6-32 x 1" nylon screws provided.

HOUSING AND FINISH

Faceplate: Flame retardant ABS plastic rated 94V-O by UL, finished in off-white and supplied with nylon mounting screws.

DIMENSIONS

Faceplate: 2-3/4" (6.99cm) wide x 4-1/2" (11.43cm) high; **W41 Backbox:** 4-11/16" (11.91cm) square electrical backbox with one gang adapter for total depth of 2-7/8" (7.30cm), supplied by others.

LISTINGS

The HM-1B/K2 (CODE BLUE) is UL and CUL listed Hospital Signaling Equipment / Nurse Call Equipment under File E157381.

Heritage Medcall, Inc.

202 East Virginia Avenue, Tampa, FL 33603
813-221-1000 (voice), 813-223-1405 (fax)
www.heritagemedcall.com

01/04 HM-1B/K2 (CODE BLUE) Issue C
Printed in U.S.A.

Architects' and Engineers' Specifications

Model HM-1B/K2 (CODE BLUE), CODE BLUE SWITCH

The wall recessed or surface mounted HM-1B/K2 (CODE BLUE) Code Blue Emergency Switch shall be available for use as a system feature input device as well as a status indicator.

Feature Input Device - As a system feature input device, the push button shall be used for feature activation.

Status Indication - To provide status indication, the lamp indicator shall illuminate to show feature activation and/or overall system status.

The HM-1B/K2 (CODE BLUE) shall be silk-screened labeled with the words "CODE BLUE" in bold blue lettering.

The button panel shall be provided with one combination pushbutton and lamp indicator. Lens colors shall be available (separately). Lamps shall be front replaceable with rated average life of 6000 hours.

The HM-1B/K2 (CODE BLUE) shall be UL and CUL listed Hospital Signaling Equipment / Nurse Call Equipment under File E157381.

The HM-1B/K2 (CODE BLUE) shall contain one latching normally-open SPST switches.

The faceplate shall be flame retardant ABS plastic rated 94V-O by UL, finished in off-white. For ease of installation, the button panel shall plug into pre-wired connectors.

Faceplate shall mount to backbox with two 6-32 x 1" nylon screws provided.

Button panel shall install into a two gang box with single gang adapter for surface or wall flush mounting. The dimensions shall be: **Faceplate** - 2-3/4" (6.99cm) wide x 4-1/2" (11.43cm) high; **W41 backbox** - 4-11/16" (11.91cm) square electrical backbox with one gang adapter for total depth of 2-7/8" (7.30cm), supplied by others.