


TECHNICAL SPECIFICATIONS

DUAL PATIENT STATION

HM-DPS



DESCRIPTION

Wall recessed or surface mounted dual patient station with individual cordset receptacles for use with remote call origination cordset. Removal of either cordset originates a call placement.

RECEPTACLES

Two cordset receptacles wired to accept 1/4" cordsets (normal call, geriatric, explosion proof) with nurse call origination facility.

CONTROLS AND INDICATORS

One combination white call placement indicator and call cancel button.

INSTALLATION

Color-coded, prewired terminations provided. Mount using only the two 6-32 x 1" nylon screws provided.

HOUSING AND FINISH

Faceplate: Flame retardant ABS plastic rated 94V-O by UL, finished in off-white supplied with nylon mounting screws.

W41 Backbox: metal backbox supplied by others.

DIMENSIONS

Faceplate: 2-3/4" (6.99cm) wide x 4-1/2" (11.43cm) high.

W41 Backbox: 4-11/16" (11.91cm) square electrical box with one-gang adapter for a total depth of 2-7/8" (7.30cm), supplied by others.

LISTINGS

The HM-DPS is UL and CUL listed Hospital Signaling Equipment / Nurse Call Equipment under File E157381.

Heritage Medcall, Inc.

202 East Virginia Avenue, Tampa, FL 33603
813-221-1000 (voice), 813-223-1405 (fax)
www.heritagemedcall.com

Printed in U.S.A.
01/04 HM-DPS Issue C

ARCHITECTS' AND ENGINEERS' SPECIFICATIONS

MODEL HM-DPS DUAL PATIENT STATION

The wall recessed or surface mounted dual patient station shall be for use with two remote call origination cordsets.

The patient station shall be provided with a white combination call placement indicator and call cancel button. Two receptacles shall be provided to accept two 1/4" type cordsets. A call shall be originated if either cordset is removed from the receptacles.

The unit shall be provided with color-coded prewired terminations for ease of installation. The faceplate shall be flame retardant ABS plastic rated 94V-O by UL. Nylon screws shall be provided to mount the faceplate.

The unit shall be UL and CUL listed Hospital Signaling Equipment / Nurse Call Equipment under File E157381.

The faceplate shall be finished in off-white. The W41 backbox shall be supplied by others. The dimensions shall be: **Faceplate:** 2-3/4" (6.99cm) wide x 4-1/2" (11.43cm) high, **W41 backbox:** 4-11/16" (11.91cm) square electrical box with one-gang adapter for total depth of 2-7/8" (7.30cm), supplied by others.